

Leather Power Reclining Loveseat with Power Headrests 1729-60PH in 204-80

FLEXSTEEL°

Miller | 1729

 $\ensuremath{\textcircled{C}}$ Flexsteel Industries, Inc. | Last Updated 02/24/2022

Miller | 1729

| 64PH 62PH 60PH 50PH | FEATURES | PRODUCT DIMENSIONS | OVERALL | | | SEAT | | | | | |
|------------------------------|-----------------------|---|---------|-------|-------|--------|-------|-------|---------------|---------------|-------------------|
| | | | Height | Width | Depth | Height | Width | Depth | Arm Height | Open Depth | Wall Clearance |
| | Flexsteel Spring Unit | | | | | | | | | | |
| • | DualFlex | Power Reclining Loveseat with Console & Power Headrests & Lumbar | 43″ | 77″ | 42″ | 20″ | 44″ | 21″ | 27″ | 72″ | 6″ |
| | Back Construction | -64PH | | | | | | | | | |
| • | Attached | Power Reclining Sofa with Power Headrests & Lumbar | 43″ | 86″ | 42″ | 20″ | 66″ | 21″ | 27″ | 72″ | 6″ |
| • | Seat Construction | -62PH | | | | | | | | | |
| | Attached | Power Reclining Loveseat with Power Headrests & Lumbar | 43″ | 65″ | 42″ | 20″ | 44″ | 21″ | 27″ | 72″ | 6″ |
| | High-Density (HC) | -60PH | | | | | | | | | |
| | | Power Recliner with Power Headrest & Lumbar -50PH | 43″ | 42″ | 42″ | 20″ | 22″ | 21″ | 27″ | 72″ | 6″ |

• Standard

o Optional

FLEXSTEEL®

Dimensions are in inches and are subject to variance. Options are subject to change without notice. © Flexsteel Industries, Inc.

Stocked Colors





204-04 Leather/Vinyl

204-80 Leather/Vinyl

Printed samples may vary from actual swatches. Please refer to swatches for actual color.

NOTES

Upholstery Material: Leather/Vinyl

Lay-flat mechanism accommodates occupants weighing up to 300 pounds.

Extended footrests.

Removable backs allow for easy lifting and maneuvering through doorways.

Center console features two cup holders and a storage compartment.

Single USB port is included on the top of the hand control.

Extended footrest.

Power allows you to smoothly recline to any position, adjust the headrests, and adjust the lumbar supports.

A single USB port is included on each power button control on styles with arms.

A home feature returns the headrest, footrest, and lumbar support to their original positions.



Home Button

The home button returns the headrest, footrest, and lumbar support to their original positions. To activate the home button, press and hold the button used to lower the footrest.